

Double Row Terminal Blocks

300 Series Kulka® 672 GP Series 600 Volts AC/DC (Class C)



306 / 672 GP 06

Specifications:

- Base, General Purpose Phenolic, 150°C (UL RTI)
- Closed Back Design
- Screws, #8-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-24 Poles
- 9/16" Centers
- Wire Range With Wire Binding Screw #10 - #14 AWG – 30 Amps
- Wire Range With Sems Pressure Screw #10 - #22 AWG Stranded Copper Wire Only, 30 Amps
- Will Accommodate Lugs for Wire Sizes #10 - #16 AWG, 30 Amps
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

MSP Catalog #	Kulka® Catalog #	# of poles	Dimensions	
			A	B
301	672 GP 01	1	1.54	1.13
302	672 GP 02	2	2.10	1.69
303	672 GP 03	3	2.66	2.25
304	672 GP 04	4	3.22	2.81
305	672 GP 05	5	3.79	3.38
306	672 GP 06	6	4.35	3.94
307	672 GP 07	7	4.91	4.50
308	672 GP 08	8	5.47	5.06
309	672 GP 09	9	6.04	5.63
310	672 GP 10	10	6.60	6.19
311	672 GP 11	11	7.16	6.75
312	672 GP 12	12	7.72	7.31
313	672 GP 13	13	8.29	7.88
314	672 GP 14	14	8.85	8.44
315	672 GP 15	15	9.41	9.00
316	672 GP 16	16	9.97	9.56
317	672 GP 17	17	10.54	10.13
318	672 GP 18	18	11.10	10.69
319	672 GP 19	19	11.66	11.25
320	672 GP 20	20	12.22	11.81
321	672 GP 21	21	12.79	12.38
322	672 GP 22	22	13.35	12.94
323	672 GP 23	23	13.91	13.50
324	672 GP 24	24	14.47	14.06

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG #	PRODUCT DESCRIPTION	PAGE REFERENCE
F1	KT55 Full Quick Connect (0° Flat)	See page 105
F2	KT56 Full Quick Connect (45° Bend)	See page 105
F3	KT57 Full Quick Connect (90° Bend)	See page 105
HF1	KT61 Half Quick Connect (0° Flat)	See page 105
HF2	KT62 Half Quick Connect (45° Bend)	See page 105
HF3	KT63 Half Quick Connect (90° Bend)	See page 105
S	ST Full Solder	See page 106
HS	3/4 ST Half Solder	See page 106
L	Y Feed Thru Solder (.437)	See page 106
LSL	YSY Feed Thru Solder (.625)	See page 106
LL 300	J 602 Line to Line Jumper	See page 107
SP	3786 SEMS Pressure Saddle Screw	See page 107
SPSE	SEMS Pressure Saddle Screw with External Tooth Lock Washer	Consult C/S
LWW	Feed Thru Wire Wrap (1.00)	Consult C/S
PSB	Phil-Slot Brass Screw	Consult C/S

Quick Connects: .032" x .250"

See pages 104-115 for terminal block accessories

