




Rack ATS, 100-120V, 15A, 5-15P In, (10) 5-15R Out
Part Number: AP7750A




[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Software & Firmware](#) [Options](#)

Output

Nominal Output Voltage	100V, 120V	
Maximum Total Current Draw per 15A Phase		
Output Connections	(10) NEMA 5-15R	

Input

Nominal Input Voltage	100V, 120V	
Input Frequency	50/60 Hz	
Regulatory Derated Input Current 12A (North America)		
Input Connections	NEMA 5-15P	
Cord Length	8 feet (2.44 meters)	
Number of Power Cords	2	
Acceptable Input Voltage	100-125 VAC	
Maximum Input Current per phase	15A	
Load Capacity	1440 VA	

Physical

Net Weight	10.35 lbs. (4.70 kg)
Maximum Height	1.72 inches (44 mm)
Maximum Width	17.00 inches (432 mm)
Maximum Depth	9.30 inches (236 mm)
Shipping Weight	14.25 lbs. (6.48 kg)
Shipping Height	4.50 inches (114 mm)
Shipping Width	23.63 inches (600 mm)
Shipping Depth	14.00 inches (356 mm)
Color	Black

Environmental

Operating Environment	23 - 113 °F (-5 - 45 °C)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-13 - 149 °F (-25 - 65 °C)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	FCC Part 15 Class A, ICES-003, PSE, TUV-C, TUV-NURTL, VCCI Class A
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
PEP	Available in Documentation tab
EOLI	Available in Documentation tab
Battery Directive	Compliant
Battery Notes	Contains Lithium Coin Cell

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.