



**APC Back-UPS Pro External Battery Pack (for 1500VA Back-UPS Pro models)**

Part Number: BR24BPG



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Options](#)

### Output

Battery Output Voltage	24
------------------------	----

### Batteries & Runtime

Battery Volt-Amp-Hour Capacity	372
--------------------------------	-----

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
--------------	--

Battery mounting	Stand alone battery stack
------------------	---------------------------

Expected Battery Life (years)	4 - 6
-------------------------------	-------

Included Battery Modules	2
--------------------------	---

RBC Quantity	1
--------------	---

### Physical

Net Weight	13.40 KG
------------	----------

Maximum Height	301.00 mm
----------------	-----------

Maximum Width	112.00 mm
---------------	-----------

Maximum Depth	382.00 mm
---------------	-----------

Shipping Weight	14.60 KG
-----------------	----------

Shipping Width	240.00 mm
----------------	-----------

Shipping Height	400.00 mm
-----------------	-----------

Shipping Depth	491.00 mm
Color	Black
<b>Environmental</b>	
Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-9000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters
<b>Conformance</b>	
Approvals	TUV
Standard warranty	2 years repair or replace
<b>Sustainable Offer Status</b>	
RoHS	Compliant
REACH	REACH: Contains No SVHCs
PEP	Available in Documentation tab
EOLI	Available in Documentation tab

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.