



APC ProtectNet standalone surge protector for 10/100/1000 Base-T Ethernet lines

Part Number: PNET1GB



[Technical Specifications](#) [Product Overview](#) [Documentation](#)

Input

Input Connections	--
-------------------	----

Surge Protection and Filtering

Peak Current Normal Mode	6.50 kAmps
Peak Current Common Mode	0.25 kAmps
NM Surge Response Time (ns)	1 ns
Data Line Protection	RJ45 10/100/1000 Base-T Ethernet protection
Data Lines Protected (multi-line only)	1-8
Let Through Voltage Rating	< 60

Physical

Net Weight	0.11 lbs. (0.05 kg)
Maximum Height	4.10 inches (104 mm)
Maximum Width	1.87 inches (47 mm)
Maximum Depth	1.10 inches (28 mm)
Shipping Weight	0.25 lbs. (0.11 kg)
Shipping Height	4.10 inches (104 mm)
Shipping Width	3.55 inches (90 mm)

Shipping Depth	1.15 inches (29 mm)
Master Carton Units	144.00
Master Carton Dimensions (Length x Width x Height)	21 x 23 x 17 inches (522 x 582 x 434 mm)
Master Carton Weight	46.20 lbs. (21.00 kg)
SCC Codes	1073130422673 1
Color	Beige
Units per Pallet	1152.00
Environmental	
Operating Environment	5 - 149 °F (-15 - 65 °C)
Operating Relative Humidity	0 - 95%
Storage Temperature	5 - 149 °F (-15 - 65 °C)
Storage Relative Humidity	0 - 95%
Conformance	
Approvals	UL 497B
Standard warranty	10 years repair or replace
Sustainable Offer Status	
RoHS	Compliant
REACH	REACH: Contains No SVHCs
Other Environmental Compliance	China RoHS

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.