



APC Smart-UPS RT 48V RM Battery Pack

Part Number: SURTA48RMXLBP2U



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Options](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Volt-Amp-Hour Capacity	864
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Enclosed battery cabinet
Expected Battery Life (years)	3 - 5
Included Battery Modules	2
RBC Quantity	2
Battery blocks per string	4

Physical

Net Weight	72.40 lbs. (32.91 kg)
Maximum Height	3.40 inches (86 mm)
Maximum Width	17.80 inches (452 mm)
Maximum Depth	22.00 inches (559 mm)
Shipping Weight	81.60 lbs. (37.09 kg)
Shipping Width	24.00 inches (610 mm)
Shipping Height	10.00 inches (254 mm)
Shipping Depth	28.75 inches (730 mm)

Rack Height	2U
Color	Black
Units per Pallet	12.00

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95% no%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-4 - 122 °F (-20 - 50 °C)
Storage Relative Humidity	0 - 95% no%
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	OSHPD
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
PEP	Available in Documentation tab
EOLI	Available in Documentation tab

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.