


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Basin Wrench
Catalogue number	4311
Date	03/04/2006

Range Description Basin Wrench				
Features <ul style="list-style-type: none"> • Telescopic pipe length adjustable to 4 set lengths between 230mm and 410mm - allows setting to the most convenient length • Sliding T handle for maximum convenience • Toothed spring loaded jaws – automatically adjust to the correct size • Forged steel jaws – strong and durable • Jaws swivel through 180 degrees – for tightening or loosening 				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4311	Basin wrench – display packed	5013969974232	82041200	6

Technical product information	Shaft and Sliding T handle – steel, mat chrome plated Jaws – Forged Steel Max jaw capacity 35mm across the hex points of a nut
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship

	Damage caused through inappropriate use is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4311	125	20	280	809	125	23	340	847

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4311	145	350	135	5195		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4311			38	Backing card			110	Box