


Capacitor, ceramic, SMD, MLCC, Array, Flex Termination, Auto Grade, 3300 pF, +/-10% Tol, 0612, 200 V, X7R



General Information	
Supplier:	KEMET
Application:	Automotive/Flexible Termination
Part Type Description:	SMD, MLCC, Array, Flex Termination, Auto Grade
Temperature Coefficient:	X7R
Body Type:	SMD Array
Termination Type:	Tin (Sn)
Chip Size:	0612
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1.6	+/-0.2
W	3.2	+/-0.2
T	0.8	+/-0.1
P	0.8	+/-0.1

Specifications	
Capacitance:	3300 pF
Voltage:	200 V
Tolerance:	+/-10%
Failure Rate:	N/A

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	4000