

PIXMA MG5750

Simply connect and print

Hassle-free printing and scanning with smart devices and the cloud. Have fun creating beautiful images and documents with this versatile, user-friendly, 5-ink All-In-One.



- Easily connect, print, scan and copy at home using this affordable, high quality 5-ink All-In-One
- Quickly and effortlessly print and scan from smart devices with the Canon PRINT app and Wi-Fi Direct®
- Experience the creative freedom of cloud printing and scanning with enhanced PIXMA Cloud Link
- Only change the colour that runs out with individual ink tanks; save using optional XL inks and auto 2-sided printing
- Control, view and connect with ease using the large, crystal clear, 6.2 cm colour display

Product Range



PIXMA MG6850 Series



PIXMA MG5750 Series



PIXMA MG4250

PIXMA MG7750 Series
PIXMA MG6850 Series
PIXMA MG5750 Series
PIXMA MG4250
PIXMA MG3650
PIXMA MG2950
PIXMA MG2450
PIXMA MG2550

Technical Specifications

GENERAL SPECIFICATIONS

Functions

Wireless Print, Copy, Scan, Cloud Link

PRINTER SPECIFICATIONS

Print Resolution

Up to 4800^[1] x 1200 dpi

Print Technology

5 Individual Ink Tanks (PGBK, BK, C, M, Y)
Inkjet FINE print head with 2pl (min.) ink droplet size
ChromaLife100 inks

Mono Print Speed

Approx. 12.6 ipm^[2]

Colour Print Speed

Approx. 9.0 ipm^[2]

Photo Print Speed

Borderless 10x15cm : Approx. 41 seconds^[3]

Borderless Printing

Yes
(A4, Letter, 20 cm x 25 cm, 13 cm x 18 cm, 10 cm x 15 cm)

Two Sided Printing

Auto Duplex Print (A4, Letter - plain paper)

CARTRIDGES AND YIELDS

Standard Ink Cartridges

5 individual ink tanks
PGI-570PGBK (Pigment Black)
CLI-571BK (Black)
CLI-571C (Cyan)
CLI-571M (Magenta)
CLI-571Y (Yellow)

Optional XL Ink Cartridges

High yield XL ink tanks
PGI-570PGBK XL (Pigment Black)
CLI-571BK XL (Black)
CLI-571C XL (Cyan)
CLI-571M XL (Magenta)
CLI-571Y XL (Yellow)

Cartridge Yield (Plain paper)

A4 Colour Document^[4]
Pigment Black: 300 pages
Pigment Black XL: 500 pages
Black: 1795* pages
Black XL: 5565* pages
Cyan: 345 pages
Cyan XL: 715 pages
Magenta: 306 pages
Magenta XL: 645 pages
Yellow: 347 pages
Yellow XL: 715 pages

Cartridge Yield (Photo print)

* Estimated supplemental yield
10 cm x 15 cm photo^[5]
Pigment Black: 2405* photos
Pigment Black XL: 4945* photos
Black: 376* photos
Black XL: 810* photos
Cyan: 121 photos
Cyan XL: 267 photos
Magenta: 136 photos
Magenta XL: 340 photos
Yellow: 127 photos
Yellow XL: 282 photos

* Estimated supplemental yield

PAPER SUPPORT

Paper Types

Plain Paper
High Resolution Paper (HR-101N)
Photo Paper Pro Platinum (PT-101)
Photo Paper Plus Glossy II (PP-201)
Photo Paper Pro Luster (LU-101)
Photo Paper Plus Semi-gloss (SG-201)
Glossy Photo Paper "Everyday Use" (GP-501)
Matte Photo Paper (MP-101)
T-Shirt Transfer
Envelope

Maximum Paper Input

Front tray: Max. 100 sheets (plain paper)

Paper Sizes

A4, A5, B5, 10 cm x 15 cm, 13 cm x 18 cm, 20 cm x 25 cm,
Envelopes (DL, COM10), Letter, Legal

Paper Weight

Plain paper: 64 - 105 g/m²
Canon photo paper: up to 300 g/m²

SCANNER SPECIFICATIONS

Scanner Type

CIS flatbed photo and document scanner

Scanner Resolution (Optical)

1200 dpi x 2400 dpi^[6]

A4 Scan Speed

Approx. 19 sec^[7]

Scanning Depth (Input / Output)

Colour: 48 bit / 24 bit
Greyscale: 16 bit / 8 bit

Maximum Document Size

216 mm x 297 mm

COPIER SPECIFICATIONS

Copy Speed

sFCOT: Approx. 20 sec^[8]
sESAT: Approx. 7.2 ipm^[8]

Multiple Copy

99 copies (max)

Copy Functions

Document Copying, Photo Copying, Borderless copy,
2-sided copy, 2-on-1 and 4-on-1 copy, Frame erase copy

Copy Zoom

25 - 400% (in 1% increments)
Fit to page
A5 to A4, B5 to A4, A4 to A5 and A4 to B5

INTERFACE

Display Type & Size

6.2cm LCD (TFT)

Interface Type - PC / Mac

33 Languages Selectable: Japanese / English (mm & inch) /
German / French / Italian / Spanish / Dutch / Portuguese /
Norwegian / Swedish / Danish / Finnish / Russian / Czech /
Hungarian / Polish / Slovene / Turkish / Greek / Simplified
Chinese / Traditional Chinese / Korean / Indonesian /
Slovakian / Estonian / Latvian / Lithuanian / Ukrainian /
Romanian / Bulgarian / Thai / Croatian / Vietnamese

Interface Type - Other

Hi-Speed USB (B Port)
Wi-Fi: IEEE802.11 b/g/n
Wi-Fi Security: WPA-PSK, WPA2-PSK, WEP, Administration
password

Technical Specifications

Interface Type - Other

PIXMA Cloud Link
 Canon PRINT Inkjet/SELPHY app
 Canon Print Service Plugin (Android)
 Google Cloud Print
 Apple AirPrint
 Wi-Fi Direct
 Access point mode
 WLAN PictBridge
 Mopria (Android)

SOFTWARE

Supported Operating Systems

Windows 8.1 (including Windows 8.1 Update),
 Windows 8
 Windows 7, Windows 7 SP1
 Windows Vista SP2
 Windows XP SP3 (32 bit only)
 Note: For Windows, .NET Framework 4 or .NET Framework 4.5 is required.
 For Windows XP, XPS Essentials Pack is required.
 Mac OS X v10.7.5 to Mac OS X v10.10

Supported Mobile Systems

iOS
 Android

Minimum System Requirements

Windows: 3GB disk space, Internet Explorer 8
 Mac: Internet connection, 1.5GB disk space, Safari 5
 Display: 1024 x 768 XGA

Software Included

MP Driver including Scanning Utility
 My Image Garden with Full HD Movie Print ^[9]
 Quick Menu
 Easy-WebPrint EX (download) ^[10]

PHYSICAL FEATURES

Weight

approx. 6.3 kg

Dimensions (W x D x H)

approx. 455 mm x 369 mm x 148 mm

Acoustic Noise Levels

approx. 43.5dB(A) ^[11]

Recommended Operating Environment

Temperature: 15-30°C
 Humidity: 10-80%RH (no dew condensation)

Power Source

AC 100-240V, 50/60Hz

Power Consumption

Off: Approx. 0.2 W
 Standby (connected to PC via USB): Approx. 0.7 W (scanning lamp off)
 Standby (all ports connected): Approx. 1.5 W (scanning lamp is off)
 Time to enter Standby mode: 7 minutes
 Copying: Approx. 12 W ^[12]

Footnotes

- [1] Ink droplets can be placed with a minimum pitch of 1/4800 inch
 [2] A4 document print speed on plain paper is measured based on average of ESAT in Office Category Test of ISO/IEC 24734 standard.
 [3] Photo print speed is based on default driver setting using ISO/JIS-SCID N2 standard on Canon Photo Paper Plus Glossy II and does not take into account data processing time on host computer.
 [4] Declared yield value in accordance with ISO/IEC 24711 standard. Values obtained by continuous printing.
 [5] Declared yield value in accordance with ISO/IEC 29102. Values obtained by continuous printing.
 [6] Optical resolution is a measure of maximum hardware sampling resolution based on ISO 14473 standard. When scanning in high resolution, the maximum scan size is restricted.
 [7] Colour document scan speed is measured with ISO/IEC 24735 Annex C Test Chart A. Scan speed indicates the time measured between pressing the scan button of the scanner driver and the on-screen status display turns off.
 [8] Colour document copy speed is measured based on average of sFCOT and sESAT in Performance Test of ISO/IEC 29183 standard.
 [9] Full HD Movie Print is available for MOV and MP4 movie files created by select Canon digital cameras and camcorders. Requires installation of software bundled with Canon video or digital camera, from which the movie was captured. MOV files require: ZoomBrowser EX / ImageBrowser (version 6.5 or later), MP4 files require: ImageBrowser EX (version 1.0 or later).
 [10] Easy-WebPrint EX requires Internet Explorer 8 or later
 [11] When printing ISO/JIS-SCID N2 pattern on 10x15cm Photo Paper Plus Glossy II using default settings.
 [12] When copying ISO/JIS-SCID N2 (printed by inkjet printer) on A4 size plain paper using default settings.

Standard disclaimers

All specifications subject to change without notice.

Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc.

Ink yield may vary depending on texts/photos printed, applications software used, print mode and type of paper used. For yield information see www.canon-europe.com/ink/yield

Scan speed may vary depending on system configuration, interface, software, scan mode settings and document size etc.

Copy speed may vary depending on document complexity, copy mode, page coverage, type of paper used etc, and does not take into account warming up time.

All brand and product names are trademarks of their respective companies.

Microsoft, Windows and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.

PIXMA MG5750

Simply connect and print

Hassle-free printing and scanning with smart devices and the cloud. Have fun creating beautiful images and documents with this versatile, user-friendly, 5-ink All-In-One.



Sales Start Date: September 2015

Product Details:

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PIXMA MG5750 Black	0557C006AA	4549292037128	£99.99 / €119.99

Ink Consumables:

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PGI-570 PGBK	0372C001AA	4549292032918	TBC
CLI-571 BK	0385C001AA	4549292032932	TBC
CLI-571 C	0386C001AA	4549292032949	TBC
CLI-571 M	0387C001AA	4549292032963	TBC
CLI-571 Y	0388C001AA	4549292032970	TBC

Optional Ink Consumables:

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PGI-570XL PGBK	0318C001AA	4549292032826	TBC
CLI-571XL BK	0331C001AA	4549292032840	TBC
CLI-571XL C	0332C001AA	4549292032857	TBC
CLI-571XL M	0333C001AA	4549292032871	TBC
CLI-571XL Y	0334C001AA	4549292032888	TBC

PIXMA MG5750

Simply connect and print

Hassle-free printing and scanning with smart devices and the cloud. Have fun creating beautiful images and documents with this versatile, user-friendly, 5-ink All-In-One.

Sales Start Date: September 2015



Measurement / Logistic Information:

Product Name	Mercury Code	Pack type	Pack description	Quantity per pack	Length (mm)	Width (mm)	Height (mm)	Net Weight (kg)	Gross Weight (kg)
PIXMA MG5750 Black	0557C006AA	EA	Each	1	522	214	480.5	6.3	8.6
		CT	Carton	20	1079	1059	965	172	174
		EP	Euro Pallet	30	1079	1059	120.6	258	261

What's in the box?

- All-In-One printer - PIXMA MG5750
- Setup Ink Tanks
- Power cord
- Setup CD-ROM (CD only for Windows – Mac drivers available online)
- Manuals and other documents