


PART NO.	BASE TYPE	DESIGN VOLTS	DESIGN AMPS	AVERAGE LIFE HOURS
LM1006MB	MINIATURE BAYONET	* 6.3 VDC	75mA	100,000

* BI-POLAR OPERATIONAL VOLTAGE 5.67 - 6.93 VDC

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
1	ISSUED	1/21/2005	D.C.
2	BI-POLAR, OPERATIONAL VOLTAGE	06/19/2008	D.C.



COLOR	PART NUMBER	LUMEN
RED	LM1006MB-R	3.80
AMBER	LM1006MB-A	1.85
WHITE	LM1006MB-W	3.10
BLUE	LM1006MB-B	0.88
GREEN	LM1006MB-G	3.85
WARM WHITE	LM1006MB-WW	2.50

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES		CEC INDUSTRIES LTD	
DECIMALS .XX ± .05		599 Bond Street Lincolnshire IL 60069	
ANGULAR ° .XXX ± .010		TITLE	
FRACTIONAL ± 1/64		TRUE 360° LED MINIATURE BAYONET BASE LAMP 6.3 VOLT DC	
DRAWN D. C.	DATE 01/21/2005	SIZE A	REV 2
CHECKED		FSCM NO.	DWG NO. LM1006MB
DESIGN		SCALE	PLOT SCALE
MATERIAL		FILE LM1006MB.dwg	SHEET 1 OF 1
		DO NOT SCALE DRAWING	