

EK EKWH 250 G NEW



Sample photo

Order symbol: EKWH 250 G NEW
Product nbr: 2538990
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074048547
EI. number:
Finland: 3420013
Electric No. Sweden: 2538090

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		760	560	250	EKW 100-G NEW	Cover	
inch:		29.9	22.0	9.8	EKWH	Base, PC	
Materials:						EKW 100-G	Cover
Material:		Polycarbonate				EKUVT	Mounting plate
Base colour:		RAL 7035 -light grey				EKUXT	Mounting plate Pertinax
Cover screws material:		Polyamide				Rating:	
Cover colour:		RAL 7035 -light grey				Ingress Protection (EN 60529): IP66/IP67	
Cover screws colour:		Grey				Impact Resistance (EN 62262): IK08/IK09	
Gasket material:		Polyurethane				Electrical insulation: Totally insulated	
Temperatures:						Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °C (short term):		-40 ... 120 °C				UV resistance: UL 508	
Temperature °C (continuous):		-40 ... 80 °C				Flammability Rating: UL 746C 5V	
Temperature °F (short term):		-40 ... 250 °F				Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °F (continuous):		-40 ... 175 °F				NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Accessories:						Certificates:	
EKWH NEW		Base, PC				Germanischer Lloyd (GL)	
						SGS Fimko	
						Lloyds Register of Shipping (LR)	
						Gost R	

