

MNX PCM 175/100 T



Sample photo

Order symbol: PCM 175/100 T
Product nbr: 6016921
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074038296
EI. number:
 Finland: 3421671
 Electric No. Denmark: 8212027255
 Electric No. Italy: 7342065
 Electric No. Sweden: 2535439

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	180	180	100	MIN 15	DIN-15 Mounting rail
inch:	7.1	7.1	3.9	MIV 15	DIN-35 Mounting rail
Materials:				FP A 175/180	Front plate (Aluminium)
Material:	Polycarbonate			HFP 180	Front plate hinge series
Base colour:	RAL 7035 -light grey			FP 22046	Wall fastening lug (4 pcs)
Cover screws material:	Polyamide			Rating:	
Cover colour:	Smoked grey			Ingress Protection (EN 60529): IP66/IP67	
Cover screws colour:	Black			Impact Resistance (EN 62262): IK08	
Gasket material:	TPE			Electrical insulation: Totally insulated	
Temperatures:				Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °C (short term):	-40 ... 120 °C			UV resistance: UL 508	
Temperature °C (continuous):	-40 ... 80 °C			Flammability Rating: UL 746C 5V	
Temperature °F (short term):	-40 ... 250 °F			Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °F (continuous):	-40 ... 175 °F			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
Accessories:				Certificates:	
MIV 175	Mounting plate (Galvanized steel)			Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

