

DESCRIPTION: M8 FEMALE - CABLE MOUNT - SOLDER CUP - 3 POS.





NOTE:

MATERIAL
 HOUSING: PBT UL94V-0, BLACK
 CONTACT: PHOSPHOR BRONZE
 GROUND: BRASS
 SHELL: BRASS
 O-RING: NBR

FINISH
 CONTACT: SILVER PLATED, 10µ Min.
 UNDER PLATE: NICKEL
 GROUND: NICKEL 60^{U+0426} BRIGHT TIN
 SHELL: NICKEL

ELECTRICAL
 RATED CURRENT: 5A
 RATED VOLTAGE: 125V
 WATER PROOF: IP67

ENVIRONMENT
 OPERATION TEMPERATURE: -40°C TO +85°C
 WIRE GAUGE: 24-28 AWG



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH

DATE: 08-21-14

CHECKED:

DATE:

NorComp

SCALE: N.T.S.

SHEET 1 OF 1

REV 0

DWG NO. 854-003-203RLS4