

169-60021



Article Number: 169-60021

Convoluted Tubing, Slit, 1" Dia., PA6, Black w/Gray Stripe, 50ft/Box



Download drawing



Download spec sheet

Base Data

Local Order Number 169-60021

Type CTN10

Color Black with Gray Stripe (BKSTGY)

- Features and Benefits**
- Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture
 - Tubing protects cables and wires against automotive fluids, vibration wear
 - Weather resistant material provides protection against water, snow, ice, and the effects of heat, cold, and sunlight

Product Description HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Short Description Convoluted Tubing, Slit, 1" Dia., PA6, Black w/Gray Stripe, 50ft/Box

Product Dimensions

Length L (Imperial)	50.0 ft
Length L (Metric)	15.2 m
Inner Diameter D (Imperial)	1.06 "
Inner Diameter D (metric)	26.92 mm
Diameter D (imperial)	1.32 "
Diameter D (metric)	33.53 mm
Diameter D2 (imperial)	1.06 "
Diameter D2 (metric)	26.92 mm
Outside Diameter D (imperial)	1.32 "
Outside Diameter D (metric)	33.53 mm
Nominal Diameter (Imperial)	1 "
Nominal Diameter (Metric)	25.40 mm
Wall Thickness WT (Imperial)	0.006 "
Wall Thickness WT (Metric)	0.152 mm

Logistics and Packaging

Quantity Per	box
Package Quantity	50.0 ft
Package Quantity (Metric)	15.2 m
Carton Quantity	2

Material and Specifications

Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	UL94 HB
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
ROHS Compliant	Yes