


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED



MATERIAL:  
 SMA: BODY: BRASS, GOLD-PLATED,  
 CENTER PIN: BRASS, GOLD-PLATED,  
 CABLE: RG174/U

THE TOLERANCE IS:  
 <1000 ±5  
 >=1000 ±10

No.	ACD No.	EAR NO.	TITLE
5	CO-174SMAR SMA-005	1525	CA SMA W/MAM RA RG174/U 5"
4	CO-174SMAR SMA-002.5	762	CA SMA W/MAM RA RG174/U 2.5"
3	CO-174SMAR SMA-001.5	457	CA SMA W/MAM RA RG174/U 1.5"
2	CO-174SMAR SMA-001	305	CA SMA W/MAM RA RG174/U 1"
1	CO-174SMAR SMA-000.6	152	CA SMA W/MAM RA RG174/U 6"

UNLESS OTHERWISE SPECIFIED EAR NO. AMPHENOL Cables on Demand  
 DIMENSIONS ARE IN INCHES 20 VALLEY ST. ENDICOTT, NY 13760  
 TOLERANCES ARE:  
 DECIMALS APPROVALS DATE  
 .0005 DRAWN/Rev U 2006-11-18  
 .001 ± .X  
 .005 ± .XX  
 .010 ± .XXX  
 .020 ± .XXX  
 .050 ± .XXX



NOTES: UNLESS OTHERWISE SPECIFIED

THIRD ANGLE PROJECTION	CHECKED	RESP ENG	DATE	SIZE DWG. NO.	REV.
				A	
MPG ENG				CO-174SMAR SMA-XXX.X	