

2.5NFP0C



Article Number: 161-05024

Spiralwrap, 3/8" Diameter, PE, Black, 100ft/RL



Download spec sheet

Base Data

Local Order Number 2.5NFP0C

Type 2.5NFP

Color Black (BK)

- Features and Benefits**
- Sheathing allows flexible routing and lead-out of cables
 - The inner edges are beveled preventing damage to cables
 - Sheathing is reusable and resistant to most chemicals
 - Spiralwrap is U.L. Recognized

Product Description HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Short Description Spiralwrap, 3/8" Diameter, PE, Black, 100ft/RL

Product Dimensions

Length L (Imperial) 100.0 ft

Length L (Metric) 30.48 m

Reel Length (imperial) 100.0 ft

Variant Spiral Binding

Bundle Diameter Min. (Imperial) 0.31 "

Bundle Diameter Min. (Metric) 7.92 mm

Bundle Diameter Max. (Imperial) 3.0 "

Bundle Diameter Max. (Metric) 76.2 mm

Diameter D (imperial) 0.375 "

Diameter D (metric) 9.53 mm

Nominal Diameter (Imperial) 3/8 "

Nominal Diameter (Metric) 9.53 mm

Wall Thickness WT (Imperial) 0.052 "

Wall Thickness WT (Metric) 1.32 mm

Pitch (imperial) 0.438 "

Pitch (metric) 11.13 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 100.0 ft

Package Quantity (Metric) 30.48 m

Carton Quantity 100.0 ft

Material and Specifications

Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	Flammable
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
ROHS Compliant	Yes
UL Recognized (US)	Yes