

GT.50X12MP2V2

Article Number: 854-44334

Grip Tie, 12"0.0"x.5", UL94V-2 Flame Rated, Polyamide; Polypropylene, Maroon, 10/pkg



Download spec sheet

Base Data

Local Order Number GT.50X12MP2V2

Type GT.50X12

Color Maroon (MN)

- Features and Benefits**
- UL94V0-2 flame rate material allow use in air handling spaces.
 - Features quick release for repetitive access to cable and wire.
 - Can be opened and closed numerous times without failure.
 - Adjustable so one size can accommodate multiple bundle sizes.

Product Description The Grip Tie is a low profile, one piece fastening device. Constructed of a hook and loop design, laminated back to back, the Grip Tie features quick release for repetitive access to cable and wire. Grip Ties are available in a variety of colors and are versatile enough for applications ranging from network installations to bundling power cords.

Short Description Grip Tie, 12"0.0"x.5", UL94V-2 Flame Rated, Polyamide; Polypropylene, Maroon, 10/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 40.0 lbs

Minimum Tensile Strength (Metric) 177.93 N

Length L (Imperial) 12.0 "

Length L (Metric) 304.8 mm

Length L2 (Imperial) 1.5 "

Length L2 (Metric) 38.1 mm

Width W (Imperial) 0.5 "

Width W (Metric) 12.7 mm

Width W2 (Imperial) 1.0 "

Width W2 (Metric) 25.4 mm

Bundle Diameter Max. (Imperial) 3.18 "

Bundle Diameter Max. (Metric) 80.772 mm

Logistics and Packaging

Quantity Per bag

Package Quantity 10

Package Quantity (Metric) 10

Carton Quantity 1000

Material and Specifications

Material Polypropylene (PP)
Polyamide 6 (PA6)

