

MB4SHA0C2

Article Number: 151-29200

Adhesive Bases, .18" Max tie width, .15" Hole Dia., 1.12" Length/Width, PA66, Black, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number MB4SHA0C2

Type MB4SHA

Color Black (BK)

Features and Benefits

- 2-way opening for use with 18 through 50 pound cable ties to provide stability when securing bundles.
- Secures using the adhesive backing and/or with one screw.

Product Description HellermannTyton's 2 way, adhesive fastened mounting base is used with 18 through 50 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by inserting one screw through the center of the mount.

Short Description Adhesive Bases, .18" Max tie width, .15" Hole Dia., 1.12" Length/Width, PA66, Black, 100/pkg

Product Dimensions

Length L (Imperial) 1.12 "

Length L (Metric) 28.3 mm

Fixation Method Screw Mounting and Adhesive

Width W (Imperial) 1.12 "

Width W (Metric) 28.3 mm

Cable Tie Width Max. (Imperial) 0.18 "

Cable Tie Width Max. (Metric) 4.6 mm

Height H (Imperial) 0.23 "

Height H (Metric) 5.8 mm

Mounting Hole Diameter D (Imperial) 0.15 "

Mounting Hole Diameter D (Metric) 3.9 mm

Thickness of Adhesive TA (Imperial) 0.031 "

Mounting Hole Diameter D Max. (Metric) 3.9 mm

Mounting Hole Diameter D Min. (Metric) 3.9 mm

Thickness of Adhesive TA (Metric) 0.8 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 4000

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Adhesive Synthetic rubber with base of polyethylene foam

Adhesive Shortcut Synthetic rubber T50

Adhesive Operating Temperature -4°F to +122°F (-20°C to +50°C)

Flammability UL94 V2 (excluding adhesive)

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes