

## RT40R0M4



**Article Number:** 115-06202

**Releasable Cable Tie, 8.5" Long, 40 lb Tensile Strength, PA66, Black, 1000/pkg**



Download spec sheet

### Base Data

**Local Order Number** RT40R0M4

**Type** RT40R

**Color** Black (BK)

- Features and Benefits**
- Special design offers a release feature for quick and easy access to wire bundles.
  - Head design provides high tensile strength with very low insertion force even after repeated use.
  - Bent tail ensures a quick and simple installation.

**Product Description** HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Releasable Cable Tie, 8.5" Long, 40 lb Tensile Strength, PA66, Black, 1000/pkg

### Product Dimensions

**Minimum Tensile Strength (Imperial)** 40.0 lbs

**Minimum Tensile Strength (Metric)** 180.0 N

**Length L (Imperial)** 8.5 "

**Length L (Metric)** 215.0 mm

**Fixation Method** None

**Identification Plate Position** none

**Releasable Closure** Yes

**Tie Closure** plastic pawl

**Variant** Inside Serrated

**Width W (Imperial)** 0.16 "

**Width W (Metric)** 4.0 mm

**Bundle Diameter Min. (Imperial)** 0.06 "

**Bundle Diameter Min. (Metric)** 1.5 mm

**Bundle Diameter Max. (Imperial)** 2.0 "

**Bundle Diameter Max. (Metric)** 51.0 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 1000

**Carton Quantity** 5000

### Material and Specifications

---

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL94 V2
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL
<b>UL Listed (US and Canada)</b>	No
<b>UL Recognized (US and Canada)</b>	Yes