

## SNP210C2



**Article Number:** 190-00101

**Snapper Hose Clamps, .353"/.398" Min/Max Diameter, POM, White, 100/pkg**



Download spec sheet

### Base Data

**Local Order Number** SNP210C2  
**Type** SNP2  
**Color** White (WH)

**Features and Benefits**

- Designed for quick, ratcheted installation and can be released and reused.
- Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.

**Product Description** HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

**Short Description** Snapper Hose Clamps, .353"/.398" Min/Max Diameter, POM, White, 100/pkg

### Product Dimensions

**Length L (Imperial)** 0.83 "

**Length L (Metric)** 21.0 mm

**Fixation Method** Plug-in mounting

**Variant** Closed

**Width W2 (Imperial)** 0.23 "

**Width W2 (Metric)** 5.84 mm

**Bundle Diameter Min. (Imperial)** 0.334 "

**Bundle Diameter Min. (Metric)** 8.7 mm

**Bundle Diameter Max. (Imperial)** 0.4 "

**Bundle Diameter Max. (Metric)** 10.0 mm

**Diameter Min. (Imperial)** 0.353 "

**Diameter Min. (Metric)** 8.97 mm

**Diameter Max. (Imperial)** 0.398 "

**Diameter Max. (Metric)** 10.11 mm

**Wall Thickness WT (Imperial)** 0.067 "

**Wall Thickness WT (Metric)** 1.7 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 100

**Carton Quantity** 8000

### Material and Specifications

**Material** Polyacetal (POM)  
**Material Shortcut** POM  
**Flammability** UL94 HB  
**Operating Temperature** -40°F to +185°F (-40°C to +85°C)  
**ROHS Compliant** Yes