

T120MR9H4

Article Number: 113-00018

Screw Mount Tie, 18lb, 4.3" Long, Max Bun Diameter 4.02", #1/4 Screw, PA66, Natural, 500/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number T120MR9H4

Type T120MR

Color Natural (NA)

Features and Benefits

- Part design applies easily to any #1/4" Screw
- Stud style provides low insertion and high extraction force.

Product Description Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.

Short Description Screw Mount Tie, 18lb, 4.3" Long, Max Bun Diameter 4.02", #1/4 Screw, PA66, Natural, 500/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 120.0 lbs

Minimum Tensile Strength (Metric) 535 N

Length L (Imperial) 15.6 "

Length L (Metric) 395.0 mm

Fixation Method fixing hole

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.3 "

Width W (Metric) 7.6 mm

Height H (Imperial) 0.31 "

Height H (Metric) 7.9 mm

Bundle Diameter Min. (Imperial) 0.2 "

Bundle Diameter Min. (Metric) 5.0 mm

Bundle Diameter Max. (Imperial) 4.0 "

Bundle Diameter Max. (Metric) 102.0 mm

Mounting Hole Diameter D (Imperial) 0.26 "

Mounting Hole Diameter D (Metric) 6.5 mm

Thickness T (Imperial) 0.07 "

Mounting Hole Diameter D Max. 6.5 mm

(Metric) Mounting Hole Diameter D Min. (Metric) 6.5 mm

Thickness T (Metric) 1.8 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	500
Carton Quantity	1000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes