

T50MR9M4



Article Number: 113-05007

Screw Mount Tie, 50 lb 8.5" Max Bundle Diameter 1.8", #10 Screw, PA66, Natural, 1.000/pkg



Download spec sheet

Base Data

Local Order Number	T50MR9M4
Type	T50MR
Color	Natural (NA)
Features and Benefits	<ul style="list-style-type: none"> • Mount design secures firmly with any #10 Screw. • Screw mount style creates low insertion and high extraction force.
Product Description	Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.
Short Description	Screw Mount Tie, 50 lb 8.5" Max Bundle Diameter 1.8", #10 Screw, PA66, Natural, 1.000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	225 N
Length L (Imperial)	8.5 "
Length L (Metric)	215.0 mm
Fixation Method	fixing hole
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18 "
Width W (Metric)	4.7 mm
Height H (Imperial)	0.22 "
Height H (Metric)	5.7 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.8 "
Bundle Diameter Max. (Metric)	45.0 mm
Mounting Hole Diameter D (Imperial)	0.21 "
Mounting Hole Diameter D (Metric)	5.4 mm
Thickness T (Imperial)	0.05 "
Mounting Hole Diameter D Max. (Metric)	5.4 mm
Mounting Hole Diameter D Min. (Metric)	5.4 mm
Thickness T (Metric)	1.2 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000
Carton Quantity	5000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes