

T50R0UVM4



Article Number: 111-04913

Standard Cable Tie, 8" Long, 50lb Tensile Strength, PA66UV, Black, 1000/pkg



Download spec sheet

Base Data

Local Order Number T50R0UVM4

Type T50R

Color Black (BK)

- Features and Benefits**
- UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures.
 - Inside serrations allow for strong hold on cables and wire bundles.
 - Head design provides high tensile strength with very low insertion force.
 - Bent tail ensures a quick and simple installation.

Product Description HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Standard Cable Tie, 8" Long, 50lb Tensile Strength, PA66UV, Black, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225.0 N

Length L (Imperial) 8.0 "

Length L (Metric) 202.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.18 "

Width W (Metric) 4.6 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 1.97 "

Bundle Diameter Max. (Metric) 50.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 1000

Carton Quantity 5000

Material and Specifications

Material	Polyamide 6.6 UV-resistant (PA66UV)
Material Shortcut	PA66UV
US MILSPEC	MS3367-1-0
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139 SAE - AS33671 Cage Code 53421
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No