

PROSAFE LED FLOATING LANTERN



» Rubber moulded push micro switch

» High-vis yellow for added safety

» Contoured easy grip handle

» Impact resistant to 1M

5 HOURS RUNTIME

160 METRE BEAM RANGE



- » 200 Lumen white Seoul LED
- » Industrial strength copolymer housing
- » Robust and weatherproof
- » Floats beam upright in water
- » Optical Beamaster lens for beam penetration
- » Ultra tough polycarbonate reflector

 BATTERY
 1 x 6v PJ996 Lantern battery (not included)

 WEIGHT
 230g (with battery)

 DIMENSION
 175 x 105mm







BEAMASTER LENS TECHNOLOGY



OPTIONAL ACCESSORIES



MOULDED RUBBER SWITCH



SMALL AND COMPACT



PROSAFE LED FLOATING LANTERN



10 HOURS RUNTIME

250 METRE BEAM RANGE 300 IP56 LUMENS OUTPUT RESISTANCE

- » 300 Lumen white Seoul LED
- » Industrial strength copolymer housing
- » Robust and weatherproof
- » Floats beam upright in water
- » Optical Beamaster lens for beam penetration
- » Ultra tough polycarbonate reflector

 BATTERY
 1 x 6v PJ996 Lantern battery (not included)

 WEIGHT
 230g (with battery)

 DIMENSION
 175 x 105mm

- » Rubber moulded push micro switch
- » High-vis yellow for added safety
- » Contoured easy grip handle
- » Impact resistant to 1M







BEAMASTER LENS TECHNOLOGY



OPTIONAL ACCESSORIES



MOULDED RUBBER SWITCH



SMALL AND COMPACT