

Outside Micrometers Series-103 INCH

Series 103

FEATURES

- Hammertone-green, baked-enamelfinished frame.
- Ratchet Stop or Friction Thimble for exact repetitive readings.
- With a standard bar except for 0-1" model



Technical Data

Graduation: .001" or .0001"
 Flatness: .000024" for models up to 12" .00004" for models over 12"
 Parallelism: [.00008 + .00004 (L/4)]" L= max range (inch)
 Measuring faces: Carbide tipped

Image	Parts	Order No	Range	Accr.	Mass	Remarks
	Parts Break Down	103-260	0-1in	±.0001in	175g	With ratchet stop
-	Parts Break Down	103-135	0-1in	±.0001in	175g	With friction thimble

103-922	-
103-907-40	-
103-908-40	

