

Digimatic Micrometer Heads Series 164

Series 164

FEATURES

- The Digimatic Micrometer Heads...
- The display can be rotated up to 330 degrees for easy reading in any position

Technical Data

Accuracy: Refer to the list of specifications.

Resolution: 0.001mm or .00005"/0.001mm

Display: LCD

Battery: SR44 (1 pc./2 pcs.*), 938882

Battery life:

1.8 years

Function

Zero-setting, Data hold, Data output, Preset, inch/mm conversion (inch/mm models)

Alarm: Low voltage, Counting value composition error

Optional Accessories

959149:SPC cable(1m/40")

959150:SPC cable(2m/80")



Inch/Metric	Metric
Range	0-2in 0-50.8mm
Order Number	164-164
Accuracy	±.00015in
Mass	490g

Pages: [1](#)