



Features:

- Replacement for halogen lamps
- Energy efficiency Class A+

Specifications:

Lamp Base Type : GU10
Average Bulb Life : 30,000 hours

Part Number Table

Description	LED Colour	Power Rating	Part Number
LED Lamp, GU10	Warm White	3.5W	LMP-M16GU10W04-06B WW
	Cool White		LMP-M16GU10W04-06B CW
	White		LMP-M16GU10W04-06B PW
	Warm White	5W	LMP-M16GU10W05-06B WW
	Cool White		LMP-M16GU10W05-06B CW
	White		LMP-M16GU10W05-06B PW

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of the Group. © Premier Farnell plc 2012.