

## 13 Pliers for Electrical Installation with tether attachment point

The all-rounder for professionals



13 82 200 T



- multifunctional pliers for the electrical installation; to grip flat and round material, for bending, deburring, cutting cable, stripping and crimping end sleeves (ferrules)
- 6 functions in one pair of pliers
- smooth surfaces near the tips grip single cores without damaging them; serrated gripping surfaces and pipe grip for gripping flat and round material
- clear-cut outside edge on the jaw for working on flush-mounted junction boxes and deburring feed-through holes
- stripping holes for conductors of 0.75 - 1.5 mm<sup>2</sup> and 2.5 mm<sup>2</sup>
- crimp die for wire-end ferrules 0.5 - 2.5 mm<sup>2</sup>
- cable shears with (induction-hardened) precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm<sup>2</sup> / dia. 15 mm
- gripping, without opening the pliers completely (intelligent latching mechanism in the spring assisted version). The cutting edge remains closed and protected
- slim dimensions for easy access
- bolted joint: precise, zero backlash operation of pliers
- High-grade special tool steel, forged, oil-hardened

### 13 82 200 T:

- Pliers with tether attachment point for mounting a fall protection

Article No.	EAN 4003773-		Pliers	Head	Handles	Ø mm	mm <sup>2</sup>	Stripping capacity for cross-sections mm <sup>2</sup>	Capacity mm <sup>2</sup>	mm	g
13 82 200 T	079972		black atramentized	polished	with multi-component grips	15,00	50,00	0,75 - 1,5 + 2,5	0,5 - 2,5	200	267

technical change and errors excepted



