

**73** **KNIPEX X-Cut® Compact Diagonal Cutter**  
with tether attachment point



**73 05 160 T**

- **Compact and 25 % less weight. Powerful and precise**
- **Cuts finest strands as well as multi-core cables and piano wires.**
- box-joint design: highest stability with low weight
- doubly supported joint axis for heaviest duty
- high cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- 40% less force required compared with standard diagonal cutters of the same length
- large opening width for thicker cables
- cuts precisely, even through fine copper wires
- compact, low-weight construction
- universally usable, in the assembly, maintenance and production
- Chrome vanadium heavy-duty steel, forged, oil-hardened

**73 05 160 T:**

- Pliers with tether attachment point for mounting a fall protection

40% less force required compared with standard diagonal cutters of the same length  
with double mounted hinged joint

Article No.	EAN 4003773-		Pliers	Handles	Ø mm	Ø mm	Ø mm	Ø mm	Ø mm	mm	g
73 05 160 T	080077		chrome plated	with multi-component grips	4,8	3,8	2,7	2,2	12,0	160	180

technical change and errors excepted

