

Keying tab - BC 53,6 BS U11 KMGY - 2896225

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Component housing, Color: light gray

Why buy this product

- Item is from the BC product range
- Conforms to DIN EN 43880
- Tool-free mounting
- Available in overall widths from one to nine width units (17.8 mm ... 161.6 mm)
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail or the wall
- Optional with bus connector for DIN rail mounting

Key Commercial Data

Packing unit	50 pc
GTIN	 4 046356 096621
Weight per Piece (excluding packing)	4.05 g
Custom tariff number	85472000
Country of origin	Germany
Product key	ACHBAZ

Technical data

General

Housing type	Component housing
Housing material	Polyamide
Color	light gray

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401

Keying tab - BC 53,6 BS U11 KMGY - 2896225

Classifications

eCl@ss

eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

UL Recognized / EAC

Ex Approvals

Approvals submitted

Approval details

UL Recognized

EAC
