









**Datenblatt - Fiche technique - Data sheet
11.04.5790**



ROLINE Mini DisplayPort Kabel, Mini DP-HDTV, ST/ST, 1,0m

ROLINE Mini DisplayPort Câble, Mini DP – HDTV, M/M, 1,0m

ROLINE Mini DisplayPort Cable, Mini DP-HDTV, M/M, 1 m



SPECIFICATION:

1. Cable: UL20276 (32AWG*1P+D+AL/MY)x5P + 32AWGx5C + AL + D + Braid(AL), Jacket PVC Black, OD=5.5±0.2mm(No LOGO)
2. Connector: Mini DP(M), Soldering Type, White Insulator, Nickel Plating
3. Connector: DP to HDTV A/M Black Insulator, PCBA, Nickel Plating
4. Inner Mold: LDPE (RoHS)-PE101
5. Outer Mold: 60P Black PVC

Table:

	Length	Tolerance
1	1000 mm	±20 mm
2	2000 mm	±30 mm
3	3000 mm	±50 mm

REV.	DATE	CONTENTS OF CHANGE	DESIGNER	TOL ±								APPROVAL	CHECK	DATE	Item No.	11.04.5790, 11.04.5791, 11.04.5792
				RANGE	Pla	Met	Ins	Por	Cab	Pac	Gas					
①				0~6	0.1	0.1	0.1	0.2	0.5	1	0.5	0.2	PHILIP	PHILIP	2015-08-18	ROLINE Mini DP Cable, Mini DP-HDTV, M/M, black
②				6~30	0.1	0.1	.15	.25	1	1	0.5	.25				
③				30~80	0.1	.15	0.2	0.3	2	1.5	1	0.3				
④				80~180	.15	.15	.25	0.3	2	2	1	.45				
⑤				180~315	.15	0.2	0.3	0.4	2.5	2	1	0.6				
				315~800	0.2	0.3	0.4	0.5	3	3	2	1.1	SCALE	1:1	UNIT	MM

