

Heavy-Duty Power Adapter Cord, 15A, 14AWG (IEC-320-C19 to NEMA 5-15P), 8-ft.

MODEL NUMBER: P034-008



Highlights

- 8-ft. C19 to 5-15P Heavy-Duty Power Cord
- 3 x 14AWG, 15A, 125V, SJTW

Package Includes

- P034-008 Heavy-Duty Power Cord

Description

Use Tripp Lite's P034-008 in server applications that require a higher rated, heavier gauge cable. IEC-60320-C19 to NEMA 5-15P connectors, 3 x 14 AWG conductors, 15A/125V rating

Features

- Molded, Heavy-Duty Power Cable, 8-ft.
- IEC-60320-C19 to NEMA 5-15P
- 14 AWG x 3C, SJTW, 15A, 125 Volt
- RoHS Compliant

Specifications

INPUT	
Cable Length (ft.)	8
Cable Length (m)	2.4
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C19
Connector B	NEMA 5-15P



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>