

TE CONNECTIVITY (TE)



Active

RPS-10-2/2.0-4

- RPS-10-2/2.0-4
- TE Internal Number: 7033790003
- Alias ID: 3-1195518-9

Always EU RoHS/ELV Compliant

- Sleeve Length (Nominal) **50.8 mm [2 in]**
- Shrink Ratio **3:1**
- Recovered Inside Diameter (Max) **4.22 mm [.166 in]**
- Expanded Inside Diameter (Min) **12.7 mm [.5 in]**
- Operating Temperature Range **-30 – 105 °C [-22 – 221 °F]**

Product Type Features

- Format **Ladder**
- Grade **Commercial**
- Product Type **Marker Sleeve**

Body Features

- Shrink Ratio **3:1**
- Sleeve Color **Yellow**
- Material **Radiation Crosslinked Polyolefin**

Dimensions

- Sleeve Length (Nominal) **50.8 mm [2 in]**
- Recovered Inside Diameter (Max) **4.22 mm [.166 in]**
- Expanded Inside Diameter (Min) **12.7 mm [.5 in]**
- Compatible Cable Diameter **4.64 – 10.79 mm [.183 – .425 in]**

- Wall Thickness (Nominal) (Full Recovery) **.61 mm [.024 in]**

Usage Conditions

- Operating Temperature Range **-30 – 105 °C [-22 – 221 °F]**