

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0732520090](#)
Status: **Active**
Overview: Precision Compression-Mount Microwave Test Connectors
Description: 50 Ohms, Precision Test Connector, 2.92mm PCB Jack, Field Replaceable, 2 Hole Flange, with 2 Screws 4.76mm, PCB Thickness 0.76-2.44mm

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	RF/Coax Connectors
Series	73252
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	2.92mm
Style	PCB
UPC	884982956018
Wire/Cable Type	N/A

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	None
Net Weight	2.058/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	Compression
Reverse Polar	No

Electrical

Impedance	50#
-----------	-----

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-73252-009
---------------	--------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

[73252](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION