



**Miniature
T&B Catalog Number:**

L-4-18-0-M

UPC Number:

72849491450

Status:

Active

Description:

Miniature Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 100.08mm (3.94 Inches), Width of 2.41mm (0.095 Inches), Thickness of 1.13mm (0.045 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	4
Length (inches)	4.0
Width (inches)	0.100
Max. Wire Bundle Diameter (inches)	5/8
Min. Wire Bundle Diameter (inches)	1/16

Specifications

Military Standard Part No.	MS-3367-4-0
Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, QC-100, L-200, L-400-C
-------------------	-------------------------------

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	25000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.66 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000218
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com