



Standard
T&B Catalog Number:

TY526M

UPC Number:

78621082549

Status:

Active

Description:

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 284.4mm (11.08 Inches), Width of 3.71mm (0.14 Inches), Thickness of 1.31mm (0.05 Inches), Tensile Strength Rating of 135 Newtons (30 pounds), Distributor Pack

Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material Nylon 6.6
 Color Natural

Dimension Information

Nominal Length (inches) 11
 Length (inches) 11.1
 Width (inches) .140
 Max. Wire Bundle Diameter (inches) 3

Specifications

Temperature Rating -40°F to 185°F
 Flammability Rating UL 94 V-2

Tooling

Application Tools ERG50, WT1-TB

Packaging

T&B Order Multiple 100
 T&B Inner Pack 100
 Package in Units 500
 Package Type Regular
 T&B Sold in UOM Each
 T&B Weight Per UOM 2.5 lbs. per 1000

Application Support

Material Selection Guide Available on Website

Available Colors

Available on Website

Certifications

RoHS Compliance

Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com