

**Standard  
T&B Catalog Number:**

TY5234MX

**UPC Number:**

78621083938

**Status:**

Active

**Description:**



Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 355.6mm (14.0 Inches), Width of 2.54mm (0.10 Inches), Thickness of 1.1mm (0.043 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds)

**Features**

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

**General**

Material Nylon 6.6 Weather Resistant  
Color Black

**Dimension Information**

Nominal Length (inches) 14  
Length (inches) 14  
Width (inches) .086  
Max. Wire Bundle Diameter (inches) 4

**Specifications**

Temperature Rating -40°F to 185°F  
Flammability Rating UL 94 V-2

**Tooling**

Application Tools ERG50, WT1-TB

**Packaging**

T&B Order Multiple 100  
T&B Inner Pack 100  
Package in Units 500  
Package Type Regular  
T&B Sold in UOM Each  
T&B Weight Per UOM 5 lbs. per 1000

**Application Support**

Material Selection Guide	Available on Website
--------------------------	----------------------

Available Colors	Available on Website
------------------	----------------------

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com