



Datasheet for part number D38999/24WH21SN

Our Catalog Part Number: D3899924WH21SN
Our Global Manufacturing Part Number: 113023-0162
Brand: Cannon Product Category: Circular Product Line: 38999 Series I, II, and III Series: KJ

Product Datasheet	
SERIES	MIL - DTL - 38999 Series III
STYLE	Jam nut receptacle
CLASS	Environment resistant (without rear accessory)
SHELL SIZE	23
SHELL MATERIAL	Corrosion resistant shells of aluminum alloy
INSULATOR MATERIAL	High grade plastic
GROMMET AND SEAL MATERIAL	Silicone base elastomer
PLATING	Olive drab cadmium over electroless nickel plate
ARRANGEMENT	23-21
NUMBER OF CONTACTS	21 contacts size 16
GENDER	Socket
CONTACT TYPE	Rear release crimp snap-in contacts
CONTACT MATERIAL	Copper Alloy, gold plate
POLARIZATION	AR° or AP° BSC=80° BR° or BP° BSC=142° CR° or CP° BSC=196°
LOW PROFILE / LIGHT WEIGHT	no
SCOOP PROOF	yes
COUPLING SYSTEM	Threaded coupling
ELECTROLYTIC EROSION	yes
DURABILITY (CYCLES)	500
HIGH IMPACT SHOCK	yes
EXTERNAL BENDING MOMENT (Size 25)	1000 in/lbs
RANDOM VIBRATION "J"	492 F
SINE VIBRATION	60 G, 85 to +392 F
SAND, DUST, ICE	yes
TEMPERATURE RANGE	65°C (85°F) to + 175°C (+347°F)
CORROSION RESISTANT	500 hours
TEST SERVICE RATING (MATED)	Sea Level = 2300 50000 ft. = 1000 70000 ft. = 1000 100000 ft. = 1000
TEST SERVICE RATING (UNMATED)	Sea Level = 2300 50000 ft. = 800 70000 ft. = 500 100000 ft. = 200
OPERATING VOLTAGE	Vrms = 767 Vdc = 1084