



Datasheet for part number CA3102E32-15SBF80F0

| |
|--|
| Our Catalog Part Number: CA3102E32-15S-B-F80-F0 |
| Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET |

| | |
|--|---|
| Product Datasheet | |
| Bayonet | Connector with bayonet coupling |
| Shell Style | Box mounting receptacle |
| Gender | Socket |
| Shell Size | 32 |
| Contact Arrangement | 32-15 |
| Number of contacts | 2 contacts size 0, 6 contacts size 12 |
| Contact Type | AWG Crimp |
| Contact Plating | Hard silver |
| Contacts included | no, delivery without contacts |
| Shielding | no |
| Contact Rating at +20 °C (68 °F) (Size 25/12) | 41 A |
| Contact Rating at +20 °C (68 °F) (Size 500/0) | 245 A |
| Contact Resistance (Size 25/12) | 3 mΩ |
| Contact Resistance (Size 500/0) | 0,2 mΩ |
| Wire Cross Section | AWG 0 (Size 0), AWG 14/12 (Size 12) |
| Operating Voltage | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41. |
| Insulator Resistance | Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ |
| Test Voltage | 2500 Vrms |
| Air and Creepage Paths (Min) | 2,8 mm |
| Ambient Temperature | Standard insulator material -55°/+125°C (-67/257°F) |
| Safety Provisions | IP67 and IP68 (1 bar pressure after 12 hrs) acc. to DIN 40 050 |
| Salt Spray Resistance | 500 hours salt spray resistant |
| Mating Cycles | 500 min |
| Sep. Force per Contact (Size 25/12) | 1,5 N |
| Sep. Force per Contact (Size 500/0) | 8,5 N |
| Gage | For infos on Gage please see catalog VG95234, part 1 |
| Coupling Torque | Closing: 19 Nm max / Opening: 1,03 Nm min |
| Contact Retention (Size 25/12) | 55 N |
| Contact Retention (Size 500/0) | 95 N |
| Shell Material | Aluminium alloy |
| Shell Plating | Olive drab chromate over cadmium plating (conductive) |
| Insulator and Grommet Material | CR-Elastomere |
| Contact Material | Copper alloy |
| Harnessing Info: Contact Cross-Section | See assembly instruction |
| Harnessing Info: Insulator Diameter | See assembly instruction |
| Wire Stripping (Size 25/12) | 6,2 mm |
| Wire Stripping (Size 500/0) | 13,7 mm |

Specifications and dimensions subject to change.



Datasheet for part number CA3102E32-15SBF80F0

| |
|--|
| Our Catalog Part Number: CA3102E32-15S-B-F80-F0 |
| Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET |

| | |
|-------------------|---|
| Product Datasheet | |
| General Info | <i>All tests in accordance with VG95319 and/or if applicable with VG95210</i> |