

H715366

VALOVÄÄNNIN, VALK., 3-AS P>-<

ZB4BK1513  
2320405  
3389110890877

### Technical information

#### ▶ Additional information

sale per indivisible quantity 1

#### ▶ Certifications and standards

standards EN/IEC 60947-1  
EN/IEC 60947-5-1  
EN/IEC 60947-5-4  
EN/IEC 60947-5-5  
JIS C 4520  
UL 508  
CSA C22.2 No 14  
product certifications BV  
CSA  
DNV  
GL  
LROS (Lloyds register of shipping)  
RINA  
UL listed

#### ▶ Compatibility

product compatibility integral LED

#### ▶ Environment

protective treatment TH  
ambient air temperature for storage -40...70 °C °C  
ambient air temperature for operation -25...70 °C °C  
class of protection against electric shock class I conforming to IEC 60536  
IP degree of protection IP69K conforming to IEC 60529  
NEMA degree of protection NEMA 13  
NEMA 4X  
IK degree of protection IK06 conforming to IEC 50102  
vibration resistance 5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6  
30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27  
50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27

#### ▶ Functional

type of operator spring return to centre  
operator profile white standard handle  
operator position information 3 positions +/- 45°  
electrical composition code M10 for <= 2 contacts using single blocks in front mounting with integral LED  
M6 for <= 2 contacts using single blocks in front mounting with integral LED and transformer  
M3 for <= 4 contacts using single blocks in front mounting with integral LED  
M4 for <= 4 contacts using single and double blocks in front mounting with integral LED

#### ▶ Performance

mechanical durability 500000 cycles cycles

#### ▶ Physical characteristics

CAD overall width 29 mm mm  
CAD overall height 29 mm mm

CAD overall depth	43 mm mm
product weight	0.036 kg kg
resistance to high pressure washer	7000000 Pa at 55 °C,distance: 0.1 m
shape of signaling unit head	round
<b>Product identification</b>	
range of product	Harmony XB4
product or component type	head for illuminated selector switch
device short name	ZB4
bezel material	chromium plated metal
mounting diameter	22 mm mm

#### Supplier information

Schneider Electric Finland Oy  
Sokerilinnantie 11 C, 02600 Espoo

+358 10 446 615

<http://www.schneider-electric.com/fi>  
[asiakaspalvelu.fi@schneider-electric.com](mailto:asiakaspalvelu.fi@schneider-electric.com)