

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640044](#)
Status: **Active**
Overview:
Description: Perma-Seal™ Butt Splice for 14-16 AWG Wire

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	19164
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	splice
Product Name	Butt, Perma-Seal™
UPC	800753113299

Physical

Barrel Type	Closed
Color - Resin	Blue
Insulation	NiAc™
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.842/g
Packaging Type	Bag
Temperature Range - Operating	-55°C to +125°C
Wire Insulation Diameter	5.97mm max.
Wire Size AWG	14, 16

Electrical

Voltage - Maximum	600V
-------------------	------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Old Part Number	SBB-16-14
-----------------	-----------

Reference - Drawing Numbers

Sales Drawing	SD-19164-017
---------------	--------------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

[19164](#) Series

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
PremiumGrade™	0640017400
Hand Crimp Tool	
Power Crimp Tool	0640057400
Head for Terminals 10-22 AWG Wire	