

ARMSTRONG® SAE 15 and 60° Full Polish Angle Wrenches

- Made in the USA - Quality and Availability
- With One Size Opening Per Wrench, One Head is Angled 15° and the Other is Angled 60° Providing 4 Different Turning Angles for Greater Access in Tight Work Areas
- Open Ends Have a Radius Design for Greater Strength; Especially When Compared to a Hex Open End
- Full Polish Chrome Finish Provides Smooth Edges with a High Luster
- Manufactured From High Alloy Steel Using the Most Up-To-Date Manufacturing Process and Heat Treat for Greater Strength and Durability
- Meets or Exceeds ASME B107.6-1994 and US Federal Spec. GGG-W-636E



Cat. No.	UPC No.	Packaging	Fastener Size	End A Width	End A Thickness	End B Width	End B Thickness	Overall Length	Product Weight	Shelf Pack Qty.
27-812	781412278125	Bagged	3/8 in	0.750 in	0.203 in	0.750 in	0.203 in	5.000 in	0.10 lb	1
27-814	781412278149	Bagged	7/16 in	0.906 in	0.250 in	0.906 in	0.250 in	5.500 in	0.14 lb	1
27-816	781412278163	Bagged	1/2 in	1.031 in	0.250 in	1.031 in	0.250 in	6.063 in	0.31 lb	1
27-818	781412278187	Bagged	9/16 in	1.188 in	0.266 in	1.188 in	0.266 in	6.500 in	0.31 lb	1
27-820	781412278200	Bagged	5/8 in	1.281 in	0.266 in	1.281 in	0.266 in	7.063 in	0.24 lb	1
27-822	781412278224	Bagged	11/16 in	1.422 in	0.297 in	1.422 in	0.297 in	7.500 in	0.32 lb	1
27-824	781412278248	Bagged	3/4 in	1.547 in	0.297 in	1.547 in	0.297 in	8.000 in	0.60 lb	1
27-826	781412278262	Bagged	13/16 in	1.672 in	0.297 in	1.672 in	0.297 in	8.563 in	0.50 lb	1
27-828	781412278286	Bagged	7/8 in	1.797 in	0.297 in	1.797 in	0.297 in	9.125 in	0.48 lb	1
27-830	781412278309	Bagged	15/16 in	1.922 in	0.297 in	1.922 in	0.297 in	9.750 in	0.56 lb	1
27-832	781412278323	Bagged	1 in	1.984 in	0.328 in	1.984 in	0.328 in	10.438 in	0.31 lb	1
27-834	781412278347	Bagged	1-1/16 in	2.125 in	0.328 in	2.125 in	0.328 in	11.188 in	0.78 lb	1
27-836	781412278361	Bagged	1-1/8 in	2.281 in	0.359 in	2.281 in	0.359 in	11.938 in	0.97 lb	1
27-840	781412278408	Bagged	1-1/4 in	2.500 in	0.359 in	2.500 in	0.359 in	12.750 in	1.17 lb	1
27-844*	781412278446	Bagged	1-3/8 in	2.625 in	0.406 in	2.625 in	0.406 in	12.500 in	1.27 lb	1
27-846*	781412278460	Bagged	1-7/16 in	2.625 in	0.406 in	2.625 in	0.406 in	12.500 in	1.26 lb	1
27-848*	781412278484	Bagged	1-1/2 in	2.625 in	0.406 in	2.625 in	0.406 in	12.500 in	1.23 lb	1
27-852*	781412278521	Bagged	1-5/8 in	3.188 in	0.453 in	3.188 in	0.453 in	15.875 in	2.07 lb	1
27-854*	781412278545	Bagged	1-11/16 in	3.313 in	0.484 in	3.313 in	0.484 in	16.563 in	2.44 lb	1
27-856*	781412278569	Bagged	1-3/4 in	3.438 in	0.500 in	3.438 in	0.500 in	17.250 in	2.63 lb	1
27-858*	781412278583	Bagged	1-13/16 in	3.563 in	0.516 in	3.563 in	0.516 in	18.000 in	2.94 lb	1
27-860*	781412278606	Bagged	1-7/8 in	3.688 in	0.547 in	3.688 in	0.547 in	18.625 in	3.55 lb	1
27-864*	781412278644	Bagged	2 in	3.922 in	0.563 in	3.922 in	0.563 in	19.250 in	5.92 lb	1

* Satin Finish