

Capacitor, film, Metallized Polypropylene, 0.068 uF, +/-10% Tol, -40/+110C, Safety: X2, 275 VAC, Lead Spacing=10 mm



**Dimensions (mm)**

Symbol	Dimension	Tolerance
L	13	+0.2
H	12	+0.1
T	6	+0.2
S	10	+/-0.4
LL	25	+2/-1
F	0.6	+/-0.05

**Packaging Specifications**

Package Kind:	Bulk
Package Quantity:	1200

**General Information**

Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	Safety: X2
Style:	Radial Box
Lead Form:	Wire Leads
Features:	Pulse
Approvals:	ENEC,UL,cUL,CQC
RoHS:	Yes

**Specifications**

Capacitance:	0.068 uF
Voltage:	560 VDC
Tolerance:	+/-10%
Voltage AC:	275 VAC
Rated Temperature:	110C
Temperature Range:	-40/+110C
Dissipation Factor @ 1 kHz:	0.1%
Insulation Resistance:	100 GOhm
Maximum dVdT:	500 v/us