


Capacitor, film, Metallized Polyester (Stacked), 1 uF, +/-10% Tol, General Purpose, 50 VDC@85C



Note: '(' correspond to the letters used in the product bulletin

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	10.2	+/-0.2
W	9.1	+/-0.2
T	5.5	+/-0.2
F	0.5	NOM

Packaging Specifications	
Package Kind:	T&R
Package Size:	Standard
Package Quantity:	800

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polyester (Stacked)
Application:	General Purpose
Style:	Surface Mount
Chip Size:	4036
RoHS:	Yes

Specifications	
Capacitance:	1 uF
Voltage:	50 VDC
Tolerance:	+/-10%
Voltage AC:	30 VAC
Rated Temperature:	85C
Temperature Range:	-55/+125C
Dissipation Factor @ 1 kHz:	0.8%
Dissipation Factor @ 10 kHz:	1.5%
Insulation Resistance:	400 MOhm
Maximum dVdT:	12 v/us