

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201098001](#)
Status: **Active**
Overview:
Description: Ultra-Lock® (M12) Ethernet Receptacle, 4 Poles, FPM M16, Female (Straight), Panel Mount, D-Code, 0.0195m (.768") Length

Agency Certification

UL E200650

General

Product Family Industrial Receptacles
 Series [120109](#)
 IP Rating IP67
 NEMA Rating NEMA 6
 Overview brad_industrial_ethernet_solutions
 Product Name Ultra-Lock® (M12)
 Type Single Ended (pigtail)
 UPC 883906516604

Physical

Coupling Type Internal Thread
 Gender Female
 Keyway D-coded
 Length 0.0195m
 Material - Component Nickel-plated Brass
 Mounting Thread Size M16 x 1.5
 Orientation Straight
 Panel Mount N/A
 Poles 4
 Temperature Range - Operating -10°C to +80°C
 Wire Size AWG 22
 Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 1.5A
 Voltage - Maximum 125V

Material Info

Old Part Number ERWAAU3000C200

Reference - Drawing Numbers

Sales Drawing SD-120109-008

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

[120109](#) Series