

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0982660326](#)  
**Status:** **Active**  
**Overview:** Premo-Flex™ Cable Jumpers  
**Description:** 0.50mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 30 Circuits, 0.152m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-98266-001 (PDF)</a>
<a href="#">Product Specification PS-98266-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Cable
Series	98266
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	<a href="#">Premo-Flex™ Cable Jumpers</a>
Product Name	Premo-Flex™FFC Jumper
UPC	756054772829

**Physical**

Cable Length	0.152m
Circuits (Loaded)	30
Net Weight	1.481/g
Packaging Type	Bag
Pitch - Termination Interface	0.50mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-98266-001
Product Specification	PS-98266-001
Sales Drawing	SD-98266-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

**China RoHS**

Green Image  
Not Relevant

**Search Parts in this Series**

[98266 Series](#)

**Use With**

<a href="www.molex.com/link/ffc-fpc.html">Molex FFC – FPC connector</a>. Be sure to match like plating