


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **5031542890**  
**Status:** **Active**  
**Overview:** CLIK-Mate™ Wire-to-Board Connectors  
**Description:** 1.50mm Pitch CLIK-Mate™ Wire-to-Board PCB Receptacle, Dual Row, Surface Mount, Vertical, Tin Plating, 28 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 5031490000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-503149-001 (PDF)</a>
<a href="#">Product Specification 5031540000 (PDF)</a>	<a href="#">Packaging Specification SPK-503154-001 (PDF)</a>
<a href="#">Product Specification PS-503154-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

UL E29179

**General**

Product Family	PCB Receptacles
Series	503154
Application	Signal, Wire-to-Board
Overview	<u>CLIK-Mate™ Wire-to-Board Connectors</u>
Product Name	CLIK-Mate™
UPC	883906426767

**Physical**

Circuits (Loaded)	28
Circuits (maximum)	28
Color - Resin	Beige
Durability (mating cycles max)	30
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	11.20mm
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2150.001/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.20mm, 1.70mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	2.0A
Voltage - Maximum	100V

**Material Info**

**Reference - Drawing Numbers**

Application Specification	5031490000, AS-503149-001
Packaging Specification	SPK-503154-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

503154 Series

**Mates With**

503149 Crimp Housing

Product Specification

5031540000, PS-503154-001, RPS-503154-001,  
RPS-503154-002, RPS-503154-003, RPS-503154-004,  
RPS-503154-005, RPS-503154-007, RPS-503154-008,  
RPS-503154-009, RPS-503154-010, RPS-503154-011,  
RPS-503154-012

Sales Drawing

SD-503154-001, SD-503154-002, SD-505406-001,  
SD-505406-002

This document was generated on 03/30/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**