



Datasheet for part number D38999/26FB35PN

Our Catalog Part Number: D3899926FB35PN
Our Global Manufacturing Part Number: 113011-0725
Brand: Cannon Product Category: Circular Product Line: 38999 Series I, II, and III Series: KJ

Product Datasheet	
SERIES	MIL - DTL - 38999 Series III
STYLE	Straight plug
CLASS	Environment resistant (without rear accessory)
SHELL SIZE	11
SHELL MATERIAL	Corrosion resistant shells of aluminum alloy
INSULATOR MATERIAL	High grade plastic
GROMMET AND SEAL MATERIAL	Silicone base elastomer
PLATING	Electroless nickel
ARRANGEMENT	11-35
NUMBER OF CONTACTS	13 contacts size 22D
GENDER	Pin
CONTACT TYPE	Rear release crimp snap-in contacts
CONTACT MATERIAL	Copper Alloy, gold plate
POLARIZATION	AR° or AP° BSC=95° BR° or BP° BSC=141° CR° or CP° BSC=208°
LOW PROFILE / LIGHT WEIGHT	no
SCOOP PROOF	yes
COUPLING SYSTEM	Threaded coupling
ELECTROLYTIC EROSION	yes
DURABILITY (CYCLES)	500
HIGH IMPACT SHOCK	yes
EXTERNAL BENDING MOMENT (Size 25)	1000 in/lbs
RANDOM VIBRATION "J"	492 F
SINE VIBRATION	60 G, 85 to +392 F
SAND, DUST, ICE	yes
TEMPERATURE RANGE	65°C (85°F) to + 200°C (+392°F)
CORROSION RESISTANT	48 hours
TEST SERVICE RATING (MATED)	Sea Level = 1300 50000 ft. = 800 70000 ft. = 800 100000 ft. = 800
TEST SERVICE RATING (UNMATED)	Sea Level = 1300 50000 ft. = 550 70000 ft. = 350 100000 ft. = 200
OPERATING VOLTAGE	Vrms = 433 Vdc = 613