

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193240007](#)
Status: **Active**
Overview: Metric Ring Terminals
Description: Avikrimp™ Metric Ring Terminal for Stud Size 5-6 (M3-3.5), Insulated Barrel

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19324](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Metric Ring Terminals](#)
 Product Name Avikrimp™
 Type Ring
 UPC 887191290072

Physical

Barrel Type Closed - Brazed
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Net Weight 0.892/g
 Packaging Type Bag
 Stud Size M3.5
 Wire Size AWG N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Old Part Number BB2,5-823-M3,5

Reference - Drawing Numbers

Sales Drawing SD-19324-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

[19324 Series](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
PremiumGrade™ Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100