



Type 124

TYPE 124

Single Pole Normally Open, or Single Pole Double Throw Contacts.
Dust Resistant and Endcaps are Isolated from Bracket

SPECIFICATIONS

Dimensions, 124-105111,-114111,-117111 3.56" L x 3.13" W x 2.19" H
 Dimensions, 124-305111,-314111 4.69" L x 3.13" W x 2.19" H
 Weight, 124-105111,-114111,-117111 16.0 oz.
 Weight, 124-305111,-314111 19.0 oz.
 Temperature Range -40° to +149°F
 Terminations, Contacts 5/16"-24 UNF-2A thread
 Terminations, Coil #10-32 UNF-2A thread
 Recommended Mounting Vertical plane with coil terminals up
 Hardware Torque, Contact Terminal 60 in. lbs. max.
 Hardware Torque, Coil Terminal 12-18 in. lbs.

Caution: A back-up wrench must be used to hold the bottom nut stationary.

Model Number	Duty Cycle	Terminal Type ①	Bracket Style	Coil Voltage D.C.	Coil Resistance (Ohms) ②	Contact Material	Contact Rating (Amps) – Inductive Load				
							Voltage D.C.	Normally Open Continuous	Inrush	Normally Closed Continuous	Inrush
124-105111	Continuous	4	Standard	12	13.2	Silver Alloy	12	100	400	–	–
124-114111	Continuous	4	Standard	24	53.0	Silver Alloy	24	100	400	–	–
124-314111	Continuous	6	Standard	24	53.0	Silver Alloy	24	100	400	50	100
124-117111	Continuous	4	Standard	36	120.0	Silver Alloy	36	100	400	–	–
124-317111	Continuous	6	Standard	36	120.0	Silver Alloy	36	100	400	50	100

① "4" = Isolated Coil, SPNO
 "6" = Isolated Coil, SPDT

② Coil resistance in Ohms @ 25°C

③ Inrush Current: Current applied within the first 1/2 second of contact closure



Type 586 SPNO

TYPE 586

Single Pole Normally Open, or Single Pole Double Throw Contacts.
Water Resistant and Case is Isolated from Bracket

SPECIFICATIONS

Dimensions, 586-114111,-117111 3.69" L x 3.30" W x 2.90" H
 Dimensions, 586-317111 4.61" L x 3.30" W x 2.90" H
 Weight, 586-114111,-117111 24.0 oz.
 Weight, 586-317111 26.0 oz.
 Temperature Range -40° to +149°F
 Terminations, Contacts 5/16"-24 UNF-2A thread
 Terminations, Coil #10-32 UNF-2A thread
 Recommended Mounting Vertical plane with coil terminals up
 Hardware Torque, Contact Terminal 60 in. lbs. max.
 Hardware Torque, Coil Terminal 12-18 in. lbs.

Model Number	Duty Cycle	Terminal Type ①	Bracket Style	Coil Voltage D.C.	Coil Resistance (Ohms) ②	Contact Material	Contact Rating (Amps) – Inductive Load				
							Voltage D.C.	Normally Open Continuous	Inrush ③	Normally Closed Continuous	Inrush ③
586-105111	Continuous	4	Standard	12	21.0	Silver Alloy	12	200	600	–	–
586-108111 ④	Continuous	4	Standard	15	32.8	Silver Alloy	15	200	600	–	–
586-114111	Continuous	4	Standard	24	84.0	Silver Alloy	24	200	600	–	–
586-117111	Continuous	4	Standard	36	189.0	Silver Alloy	36	200	600	–	–
586-120111	Continuous	4	Standard	48	336.0	Silver Alloy	36	200	600	–	–
586-314111	Continuous	6	Standard	24	84.0	Silver Alloy	24	200	600	100	200
586-317111	Continuous	6	Standard	36	120.0	Silver Alloy	36	200	600	100	200

① "4" = Isolated Coil, SPNO
 "6" = Isolated Coil, SPDT

② Coil resistance in Ohms @ 25°C

③ Inrush Current: Current applied within the first 1/2 second of contact closure

④ Ideal for 12V charging systems

NOTE: CAUTION must be used in coil selection for use in 12 volt systems where battery charging may expose coil to continuous, higher-than-rated voltage. 15 volt coils are recommended. White-Rodgers will not be responsible for consequences of misapplied solenoids.

RELAYS and TRANSFORMERS