

LED Spotlights



VT-1942

HIGHLIGHTS :

WATTS



1.5

EQ. WATTS



20

LUMINOUS



100

BEAM ANGLE



300

Item No	: VT-1942
SKU Code	: 4393
Watts	: 1.5
EQ Watts	: 20
Base / holder	: G4
Voltage	: AC/DC:12V,50Hz
Lumen(lm)	: 100
Color Temperature	: 6000K
Beam Angle	: 300
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: PLASTIC
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800157604178
Unit size	: D:10x40mm
Packing details	: 500
Unit cbm	: 3E-05

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Non – Flickering
- Excellent Heat Radiation Efficiency
- Customized exterior for stronger body
- Perfect choice for Exhibition Stands,Hotels, Bars, Commercial & Residential Lighting

CLICK HERE
FOR OTHER RELATED CERTIFICATES 